



Indoor Luminaire Photometric Data

Description Information

Luminary Name: 55252		Lum. Catalog:	Test ID:
Lamp Name:		Lamp Catalog:	Test Date: 2025/04/01
Manufacture:		Shld. Ang(°):	Test Machine:GON-2000
Test Lab:		Frequency (Hz):	Lamp CCT(K): 3000 Ra: 82
Lum. Size(W*L*H):0.050m*-0.050m*0.000m		Lum. Area(m2):0.002	Lum. W(kg): 0.000
Test System: C, γ	Test Step: C=30.0 γ=1.0	Temp. (°C): 25	Humidity(%): 50.0


Character Parameter

Lamp Speciality Parameter		Luminaire Speciality Parameter	
Rated Flux(lm): 239.990		Luminary Flux(lm): 239.986	Field Angle(10%Imax): 91.3(°)
Rated Power(W): 3		Luminary Efficiency: 100.00%	Down Lumens&Percent: 239.986lm 100.00%
Rated Voltage(V): 220		Luminary EER(lm/W): 84.294	Up Lumens&Percent: 0.000lm 0.00%
Tested Power(W): 2.847		Max. Candela(cd): 260.831	S/MH: C0_a180=0.874 C90_270=0.885
Lamps' Inside: 1		Max Cand@Ang. (°): C=240.0 γ=1.0	CIE Type: Semi-Direct
Tested Electrics(V, A, pf):229.2, 0.025, 0.479		Beam Angle(50%Imax): 58.8(°)	ErP Φ use(90°): 231.465lm
Lamp Size(W*L*H):0.050m*-0.050m*0.000m		Left=-30.1°, Right=28.7°	IRF(%): 244.040



2D Plane Light Intensity Distribution Curve


Lum. Name: 55252	Lum. Catalog:	Test ID:
Lamp Name:	Lamp Catalog:	Test Lab:
Manufacture:	Test Machine:GON-2000	Test Date: 2025/04/01



3D Light Intensity Distribution Modal

Lum. Name:55252	Lum. Catelog:	Test ID:
Lamp Name:	Lamp Catelog:	Test Lab:
Manufacture:	Test Machine:GON-2000	Test Date: 2025/04/01

3D Light Intensity Distribution Modal



Curves:

View Angles:

3D Model

Orient:0

Fixture

Tilt:0

Vert. HUD

Roll:0

Hori. HUD

Spin:0

**Photometric Filename:GL-3W-COB-0300-MH-60D-3000K-老化前.IES**


Zone(γ)	Zone Flux (1m)	Sums Flux (1m)	Zone%Lamp	Sums%Lamp	Zone(γ)	Zone Flux (1m)	Sums Flux (1m)	Zone%Lamp	Sums%Lamp
0.0-1.0	0.25	0.25	0.10	0.10	47.0-48.0	1.55	234.44	0.65	97.69
1.0-2.0	0.75	0.99	0.31	0.41	48.0-49.0	1.32	235.75	0.55	98.23
2.0-3.0	1.24	2.23	0.52	0.93	49.0-50.0	1.10	236.85	0.46	98.69
3.0-4.0	1.73	3.96	0.72	1.65	50.0-51.0	0.90	237.75	0.37	99.07
4.0-5.0	2.21	6.17	0.92	2.57	51.0-52.0	0.71	238.46	0.30	99.36
5.0-6.0	2.68	8.84	1.11	3.68	52.0-53.0	0.54	239.01	0.23	99.59
6.0-7.0	3.13	11.97	1.31	4.99	53.0-54.0	0.39	239.40	0.16	99.75
7.0-8.0	3.58	15.55	1.49	6.48	54.0-55.0	0.26	239.66	0.11	99.86
8.0-9.0	4.00	19.55	1.67	8.15	55.0-56.0	0.17	239.83	0.07	99.93
9.0-10.0	4.41	23.96	1.84	9.98	56.0-57.0	0.10	239.93	0.04	99.97
10.0-11.0	4.80	28.76	2.00	11.98	57.0-58.0	0.04	239.97	0.02	99.99
11.0-12.0	5.16	33.92	2.15	14.13	58.0-59.0	0.01	239.98	0.01	100.00
12.0-13.0	5.50	39.41	2.29	16.42	59.0-60.0	0.00	239.99	0.00	100.00
13.0-14.0	5.81	45.23	2.42	18.85	60.0-61.0	0.00	239.99	0.00	100.00
14.0-15.0	6.10	51.33	2.54	21.39	61.0-62.0	0.00	239.99	0.00	100.00
15.0-16.0	6.36	57.69	2.65	24.04	62.0-63.0	0.00	239.99	0.00	100.00
16.0-17.0	6.60	64.28	2.75	26.79	63.0-64.0	0.00	239.99	0.00	100.00
17.0-18.0	6.81	71.09	2.84	29.62	64.0-65.0	0.00	239.99	0.00	100.00
18.0-19.0	6.99	78.08	2.91	32.54	65.0-66.0	0.00	239.99	0.00	100.00
19.0-20.0	7.15	85.23	2.98	35.51	66.0-67.0	0.00	239.99	0.00	100.00
20.0-21.0	7.27	92.50	3.03	38.54	67.0-68.0	0.00	239.99	0.00	100.00
21.0-22.0	7.37	99.87	3.07	41.61	68.0-69.0	0.00	239.99	0.00	100.00
22.0-23.0	7.43	107.30	3.10	44.71	69.0-70.0	0.00	239.99	0.00	100.00
23.0-24.0	7.46	114.76	3.11	47.82	70.0-71.0	0.00	239.99	0.00	100.00
24.0-25.0	7.46	122.22	3.11	50.93	71.0-72.0	0.00	239.99	0.00	100.00
25.0-26.0	7.43	129.65	3.09	54.02	72.0-73.0	0.00	239.99	0.00	100.00
26.0-27.0	7.36	137.01	3.07	57.09	73.0-74.0	0.00	239.99	0.00	100.00
27.0-28.0	7.26	144.27	3.03	60.12	74.0-75.0	0.00	239.99	0.00	100.00
28.0-29.0	7.13	151.41	2.97	63.09	75.0-76.0	0.00	239.99	0.00	100.00
29.0-30.0	6.97	158.38	2.91	65.99	76.0-77.0	0.00	239.99	0.00	100.00
30.0-31.0	6.78	165.16	2.83	68.82	77.0-78.0	0.00	239.99	0.00	100.00
31.0-32.0	6.57	171.73	2.74	71.56	78.0-79.0	0.00	239.99	0.00	100.00
32.0-33.0	6.33	178.06	2.64	74.19	79.0-80.0	0.00	239.99	0.00	100.00
33.0-34.0	6.06	184.12	2.53	76.72	80.0-81.0	0.00	239.99	0.00	100.00
34.0-35.0	5.77	189.89	2.41	79.13	81.0-82.0	0.00	239.99	0.00	100.00
35.0-36.0	5.46	195.35	2.28	81.40	82.0-83.0	0.00	239.99	0.00	100.00
36.0-37.0	5.13	200.49	2.14	83.54	83.0-				

Zonal Flux Tabulation - (Cont.)

Zone(γ)	Zone Flux (lm)	Sums Flux (lm)	Zone%Lamp	Sums%Lamp	Zone(γ)	Zone Flux (lm)	Sums Flux (lm)	Zone%Lamp	Sums%Lamp
94.0-95.0	0.00	239.99	0.00	100.00	141.0-142.0	0.00	239.99	0.00	100.00
95.0-96.0	0.00	239.99	0.00	100.00	142.0-143.0	0.00	239.99	0.00	100.00
96.0-97.0	0.00	239.99	0.00	100.00	143.0-144.0	0.00	239.99	0.00	100.00
97.0-98.0	0.00	239.99	0.00	100.00	144.0-145.0	0.00	239.99	0.00	100.00
98.0-99.0	0.00	239.99	0.00	100.00	145.0-146.0	0.00	239.99	0.00	100.00
99.0-100.0	0.00	239.99	0.00	100.00	146.0-147.0	0.00	239.99	0.00	100.00
100.0-101.0	0.00	239.99	0.00	100.00	147.0-148.0	0.00	239.99	0.00	100.00
101.0-102.0	0.00	239.99	0.00	100.00	148.0-149.0	0.00	239.99	0.00	100.00
102.0-103.0	0.00	239.99	0.00	100.00	149.0-150.0	0.00	239.99	0.00	100.00
103.0-104.0	0.00	239.99	0.00	100.00	150.0-151.0	0.00	239.99	0.00	100.00
104.0-105.0	0.00	239.99	0.00	100.00	151.0-152.0	0.00	239.99	0.00	100.00
105.0-106.0	0.00	239.99	0.00	100.00	152.0-153.0	0.00	239.99	0.00	100.00
106.0-107.0	0.00	239.99	0.00	100.00	153.0-154.0	0.00	239.99	0.00	100.00
107.0-108.0	0.00	239.99	0.00	100.00	154.0-155.0	0.00	239.99	0.00	100.00
108.0-109.0	0.00	239.99	0.00	100.00	155.0-156.0	0.00	239.99	0.00	100.00
109.0-110.0	0.00	239.99	0.00	100.00	156.0-157.0	0.00	239.99	0.00	100.00
110.0-111.0	0.00	239.99	0.00	100.00	157.0-158.0	0.00	239.99	0.00	100.00
111.0-112.0	0.00	239.99	0.00	100.00	158.0-159.0	0.00	239.99	0.00	100.00
112.0-113.0	0.00	239.99	0.00	100.00	159.0-160.0	0.00	239.99	0.00	100.00
113.0-114.0	0.00	239.99	0.00	100.00	160.0-161.0	0.00	239.99	0.00	100.00
114.0-115.0	0.00	239.99	0.00	100.00	161.0-162.0	0.00	239.99	0.00	100.00
115.0-116.0	0.00	239.99	0.00	100.00	162.0-163.0	0.00	239.99	0.00	100.00
116.0-117.0	0.00	239.99	0.00	100.00	163.0-164.0	0.00	239.99	0.00	100.00
117.0-118.0	0.00	239.99	0.00	100.00	164.0-165.0	0.00	239.99	0.00	100.00
118.0-119.0	0.00	239.99	0.00	100.00	165.0-166.0	0.00	239.99	0.00	100.00
119.0-120.0	0.00	239.99	0.00	100.00	166.0-167.0	0.00	239.99	0.00	100.00
120.0-121.0	0.00	239.99	0.00	100.00	167.0-168.0	0.00	239.99	0.00	100.00
121.0-122.0	0.00	239.99	0.00	100.00	168.0-169.0	0.00	239.99	0.00	100.00
122.0-123.0	0.00	239.99	0.00	100.00	169.0-170.0	0.00	239.99	0.00	100.00
123.0-124.0	0.00	239.99	0.00	100.00	170.0-171.0	0.00	239.99	0.00	100.00
124.0-125.0	0.00	239.99	0.00	100.00	171.0-172.0	0.00	239.99	0.00	100.00
125.0-126.0	0.00	239.99	0.00	100.00	172.0-173.0	0.00	239.99	0.00	100.00
126.0-127.0	0.00	239.99	0.00	100.00	173.0-174.0	0.00	239.99	0.00	100.00
127.0-128.0	0.00	239.99	0.00	100.00	174.0-175.0	0.00	239.99	0.00	100.00
128.0-129.0	0.00	239.99	0.00	100.00	175.0-176.0	0.00	239.99	0.00	100.00
129.0-130.0	0.00	239.99	0.00	100.00	176.0-177.0	0.00	239.99	0.00	100.00
130.0-131.0	0.00	239.99	0.00	100.00	177.0-178.0	0.00	239.99	0.00	100.00
131.0-132.0	0.00	239.99	0.00	100.00	178.0-179.0	0.00	239.99	0.00	100.00
132.0-133.0	0.00	239.99	0.00	100.00	179.0-180.0	0.00	239.99	0.00	100.00
133.0-134.0	0.00	239.99	0.00	100.00					
134.0-135.0	0.00	239.99	0.00	100.00					
135.0-136.0	0.00	239.99	0.00	100.00					
136.0-137.0	0.00	239.99	0.00	100.00					
137.0-138.0	0.00	239.99	0.00	100.00					
138.0-139.0	0.00	239.99	0.00	100.00					
139.0-140.0	0.00	239.99	0.00	100.00					
140.0-141.0	0.00	239.99	0.00	100.00					

Rectangle ISO Lighting Intensity Diagram

Lum. Name: 55252	Lum. Catalog:	Test ID:
Lamp Name:	Lamp Catalog:	Test Lab:
Manufacture:	Test Machine:GON-2000	Test Date: 2025/04/01




Maximum Light Intensity(cd): 260.83  
Maximum Cand.@Angle: H=-0.5°,V=-0.9°

**Photometric Filename:GL-3W-COB-0300-MH-60D-3000K-老化前.IES**

## Plane ISO-Illuminance Diagram

Lum. Name: 55252	Lum. Catelog:	Test ID:
Lamp Name:	Lamp Catelog:	Test Lab:
Manufacture:	Test Machine:GON-2000	Test Date: 2025/04/01

### Plane ISO-Illuminance Curve



Working Plane Luminaire Mounting Height(m): 3.00


Working Plane Maximum Illuminance(lx): 28.97

Working Plane Maximum Illuminance Position(d/h):H-0.0 V-0.0

3D Plane ISO Illuminance Diagram

Lum. Name: 55252	Lum. Catalog:	Test ID:
Lamp Name:	Lamp Catalog:	Test Lab:
Manufacture:	Test Machine:GON-2000	Test Date: 2025/04/01

3D Plane Illuminance Modal






Space ISO Illuminance Diagram

Lum. Name:55252	Lum. Catalog:	Test ID:
Lamp Name:	Lamp Catalog:	Test Lab:
Manufacture:	Test Machine:GON-2000	Test Date: 2025/04/01


Space ISO Illuminance Curve



Space Plane Maximum Illuminance and @Angle:260.13lx,0.0deg  
Plane Maximum Lighting Intensity and @Angle:260.131cd,0eg

Illuminance-Distance Diagram

Lum. Name:55252	Lum. Catelog:	Test ID:
Lamp Name:	Lamp Catelog:	Test Lab:
Manufacture:	Test Machine:GON-2000	Test Date: 2025/04/01



Indoor Luminance Limiting Curves

Lum. Name:55252	Lum. Catalog:	Test ID:
Lamp Name:	Lamp Catalog:	Test Lab:
Manufacture:	Test Machine:GON-2000	Test Date: 2025/04/01


Glare Grade Table

GI	Quality	Using Illuminance							
1.15	A	2000	1000	500	<=300				
1.5	B		2000	1000	500	<=300			
1.85	C			2000	1000	500	<=300		
2.2	D				2000	1000	500	<=300	
2.55	E	a				2000	1000	500	<=300
			b	c	d	e	f	g	h

Luminance Table

Gama (deg)	45	50	55	60	65	70	75	80	85
C0	10974	3288	0	0	0	0	0	0	0
C90	28635	14469	4823	0	0	0	0	0	0

Luminance Limiting Curve




Luminous Size: Length(m)=-0.050 Width(m)=-0.050 Height(m)=0.000 Area(m^2)=0.001963

Luminous Type: Without Luminous Side

Luminous Curves: C0-C180 Color: C90-C270 Color:

Indoor Budgetary Estimate Table

Lum. Name:55252	Lum. Catalog:	Test ID:
Lamp Name:	Lamp Catalog:	Test Lab:
Manufacture:	Test Machine:GON-2000	Test Date: 2025/04/01



Indoor Coefficient of Utilization Table

Lum. Name:55252	Lum. Catelog:	Test ID:
Lamp Name:	Lamp Catelog:	Test Lab:
Manufacture:	Test Machine:GON-2000	Test Date: 2025/04/01

Coefficients of Utilization – Zonal Cavity Method																		
Coef.	Effective Floor Cavity Reflectance RFC=0.20																	
RhoCC (%)	80				70				50			30			10			0
RhoW (%)	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR	Coefficient of Utilization(%)																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	59
8	78	68	62	58	77	68	62	58	66	61	57	65	61	57	64	60	57	55
9	74	64	58	54	73	64	58	54	63	57	54	62	57	53	61	57	53	52
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49

Unified Glare Rating Table

Lum. Name:55252	Lum. Catelog:	Test ID:
Lamp Name:	Lamp Catelog:	Test Lab:
Manufacture:	Test Machine:GON-2000	Test Date: 2025/04/01

Unified Glare Rating Table

Ceiling RCC		0.70	0.70	0.50	0.50	0.30	0.70	0.70	0.50	0.50	0.30
Wall RW		0.50	0.30	0.50	0.30	0.30	0.50	0.30	0.50	0.30	0.30
Floor RFC		0.20	0.20	0.20	0.20	0.20	0.20	0.20	0.20	0.20	0.20
Room Size		Vewed crosswise					Vewed endwise				
X=2H	Y=2H	17.5	18.5	17.8	18.8	19.1	20.2	21.2	20.6	21.5	21.8
	Y=3H	17.3	18.1	17.7	18.5	18.8	20.0	20.9	20.4	21.2	21.6
	Y=4H	17.2	18.0	17.6	18.3	18.7	19.9	20.7	20.3	21.1	21.5
	Y=6H	17.1	17.8	17.5	18.2	18.6	19.8	20.5	20.2	20.9	21.3
	Y=8H	17.0	17.7	17.5	18.1	18.5	19.8	20.4	20.2	20.8	21.2
	Y=12H	17.0	17.6	17.4	18.0	18.4	19.7	20.4	20.1	20.7	21.2
X=4H	Y=2H	17.2	18.0	17.6	18.3	18.7	19.9	20.7	20.3	21.1	21.5
	Y=3H	17.0	17.6	17.4	18.0	18.4	19.7	20.4	20.2	20.8	21.2
	Y=4H	16.9	17.4	17.3	17.9	18.3	19.6	20.2	20.1	20.6	21.1
	Y=6H	16.8	17.2	17.2	17.7	18.2	19.5	20.0	20.0	20.4	20.9
	Y=8H	16.7	17.1	17.2	17.6	18.1	19.4	19.9	19.9	20.3	20.8
	Y=12H	16.6	17.0	17.1	17.5	18.0	19.4	19.7	19.9	20.2	20.7
X=8H	Y=4H	16.7	17.1	17.2	17.6	18.1	19.4	19.9	19.9	20.3	20.8
	Y=6H	16.6	16.9	17.1	17.4	17.9	19.3	19.7	19.8	20.2	20.7
	Y=8H	16.5	16.8	17.0	17.3	17.8	19.2	19.5	19.8	20.1	20.6
	Y=12H	16.4	16.7	17.0	17.2	17.8	19.2	19.4	19.7	19.9	20.5
X=12H	Y=4H	16.6	17.0	17.1	17.5	18.0	19.4	19.7	19.9	20.2	20.7
	Y=6H	16.5	16.8	17.0	17.3	17.8	19.2	19.5	19.8	20.0	20.6
	Y=8H	16.4	16.7	17.0	17.2	17.8	19.2	19.4	19.7	19.9	20.5
Variations with the objverver position at spacings											
S=1.0H		0.0/0.0					0.0/0.0				
S=1.5H		0.0/0.0					0.0/0.0				
S=2.0H		0.0/0.0					0.0/0.0				
Reduced UGR Table:											
Nordic Standard Table:		BK0					BK0				
Correction Value		0.0					0.0				

o the CIE Pub.117, data has been corrected, refers to the lamp's lumens 8.2flm.

IES Indoor Report

Photometric Filename:GL-3W-COB-0300-MH-60D-3000K-老化前.IES

Candela Tabulation

V/H	C0. 0	C30. 0	C60. 0	C90. 0	C120. 0	C150. 0	C180. 0	C210. 0	C240. 0	C270. 0	C300. 0	C330. 0
γ 0. 0	260. 13	260. 13	260. 13	260. 13	260. 13	260. 13	260. 13	260. 13	260. 13	260. 13	260. 13	260. 13
γ 1. 0	257. 30	259. 58	260. 75	260. 71	260. 65	260. 30	260. 00	260. 51	260. 83	260. 58	260. 50	259. 91
γ 2. 0	255. 15	258. 49	260. 26	260. 42	260. 44	260. 31	260. 81	260. 31	260. 13	259. 60	259. 63	259. 23
γ 3. 0	252. 55	257. 05	259. 48	260. 16	260. 12	259. 96	260. 78	259. 52	258. 69	257. 74	258. 04	257. 87
γ 4. 0	249. 87	255. 27	258. 58	260. 03	259. 86	259. 31	260. 58	258. 44	256. 95	255. 56	255. 97	256. 12
γ 5. 0	246. 74	253. 19	257. 27	259. 59	259. 39	258. 07	260. 20	257. 00	254. 83	252. 93	253. 44	253. 79
γ 6. 0	243. 28	250. 79	255. 51	258. 86	258. 55	256. 67	259. 48	255. 34	252. 38	249. 95	250. 38	250. 96
γ 7. 0	239. 52	247. 83	253. 44	257. 57	257. 42	254. 91	258. 61	253. 50	249. 89	246. 61	246. 98	247. 80
γ 8. 0	235. 30	244. 68	250. 99	255. 84	255. 69	252. 45	257. 27	251. 21	246. 97	243. 10	243. 37	244. 29
γ 9. 0	230. 91	241. 10	248. 01	253. 84	253. 34	249. 79	255. 56	248. 48	243. 66	239. 28	239. 46	240. 47
γ 10. 0	226. 44	237. 33	244. 86	251. 26	250. 59	246. 55	253. 24	245. 36	239. 93	235. 24	235. 57	236. 42
γ 11. 0	221. 60	233. 21	241. 29	248. 17	247. 51	243. 02	250. 71	241. 95	235. 82	230. 70	231. 15	232. 10
γ 12. 0	216. 69	228. 71	237. 14	244. 64	244. 04	238. 99	247. 53	238. 13	231. 33	225. 92	226. 35	227. 64
γ 13. 0	211. 27	224. 01	232. 68	240. 55	240. 19	234. 78	244. 03	233. 80	226. 52	220. 90	221. 32	222. 69
γ 14. 0	205. 88	218. 96	227. 97	236. 48	236. 07	230. 14	240. 03	229. 24	221. 65	215. 72	216. 04	217. 71
γ 15. 0	200. 21	213. 57	222. 97	231. 98	231. 50	225. 32	235. 92	224. 51	216. 60	210. 29	210. 53	212. 29
γ 16. 0	194. 25	208. 00	217. 90	227. 29	227. 00	220. 62	231. 41	219. 63	211. 37	204. 82	204. 79	206. 80
γ 17. 0	188. 40	202. 00	212. 60	222. 24	222. 09	215. 77	226. 84	214. 38	205. 96	199. 47	198. 98	201. 21
γ 18. 0	182. 31	195. 97	207. 14	217. 14	217. 18	210. 72	222. 15	209. 23	200. 64	194. 07	192. 92	195. 60
γ 19. 0	176. 05	189. 97	201. 57	211. 65	211. 75	205. 52	217. 13	203. 76	195. 07	188. 19	186. 61	189. 84
γ 20. 0	169. 83	183. 88	195. 99	206. 32	206. 13	200. 17	211. 89	198. 13	189. 49	182. 05	180. 08	183. 95
γ 21. 0	163. 54	177. 71	190. 48	200. 78	200. 36	194. 61	206. 50	192. 23	183. 52	175. 50	173. 41	177. 74
γ 22. 0	156. 82	171. 46	184. 85	194. 91	194. 44	188. 72	200. 74	186. 17	177. 38	168. 96	166. 66	171. 37
γ 23. 0	149. 89	164. 92	179. 07	188. 91	188. 23	182. 43	194. 84	180. 06	170. 81	162. 23	160. 14	164. 74
γ 24. 0	142. 99	158. 74	173. 06	182. 69	181. 81	175. 80	188. 82	173. 71	164. 16	155. 48	153. 23	158. 08
γ 25. 0	135. 91	152. 37	166. 48	176. 50	175. 34	169. 11	182. 73	167. 14	157. 15	148. 35	146. 46	151. 26
γ 26. 0	128. 87	145. 81	159. 73	169. 99	168. 69	162. 04	176. 56	160. 25	150. 11	141. 16	139. 47	144. 14
γ 27. 0	121. 80	139. 17	153. 13	163. 29	161. 93	154. 85	170. 17	153. 39	142. 83	133. 73	132. 58	137. 12
γ 28. 0	114. 57	132. 10	146. 04	156. 40	154. 86	147. 54	163. 47	146. 40	135. 67	126. 53	125. 50	130. 02
γ 29. 0	107. 50	125. 08	138. 76	149. 42	147. 74	140. 18	156. 37	139. 37	128. 46	119. 21	118. 47	122. 87
γ 30. 0	100. 21	117. 74	131. 27	142. 14	140. 41	133. 01	149. 09	132. 18	121. 06	111. 92	111. 27	115. 71
γ 31. 0	92. 99	110. 56	124. 00	135. 05	133. 20	125. 81	141. 99	124. 88	113. 68	104. 53	103. 93	108. 50
γ 32. 0	85. 84	103. 31	116. 84	127. 84	125. 91	118. 60	134. 60	117. 50	106. 18	97. 24	96. 68	101. 30
γ 33. 0	78. 97	96. 07	109. 82	120. 65	118. 55	111. 35	127. 28	110. 15	98. 90	89. 99	89. 58	94. 09
γ 34. 0	71. 93	89. 07	102. 70	113. 37	111. 13	103. 90	119. 80	102. 75	91. 47	82. 79	82. 41	87. 10
γ 35. 0	65. 07	82. 13	95. 52	106. 00	103. 54	96. 58	112. 35	95. 39	84. 20	75. 63	75. 46	80. 05
γ 36. 0	58. 47	75. 25	88. 18	98. 74	96. 03	89. 33	104. 73	87. 93	77. 25	68. 64	68. 65	73. 14
γ 37. 0	52. 09	68. 33	81. 10	91. 53	88. 64	82. 15	97. 20	80. 68	70. 28	61. 59	61. 90	66. 29
γ 38. 0	45. 97	61. 67	74. 32	84. 57	81. 54	75. 20	89. 76	73. 58	63. 61	54. 95	55. 31	59. 57
γ 39. 0	40. 26	55. 34	67. 55	77. 61	74. 50	68. 38	82. 56	66. 68	57. 08	48. 54	49. 18	53. 10
γ 40. 0	34. 85	49. 10	60. 96	70. 73	67. 68	61. 73	75. 43	60. 03	50. 82	42. 67	43. 21	47. 14
γ 41. 0	29. 95	43. 16	54. 66	63. 99	61. 03	55. 33	68. 68	53. 59	44. 86	37. 22	37. 76	41. 34
γ 42. 0	25. 62	37. 62	48. 45	57. 49	54. 60	49. 15	61. 94	47. 44	39. 23	32. 16	32. 54	35. 82
γ 43. 0	21. 66	32. 52	42. 74	51. 23	48. 48	43. 40	55. 39	41. 60	34. 21	27. 66	27. 79	30. 85
γ 44. 0	18. 17	27. 98	37. 43	45. 31	42. 69	38. 04	49. 28	36. 27	29. 53	23. 49	23. 62	26. 42
γ 45. 0	15. 24	23. 69	32. 42	39. 76	37. 39	33. 10	43. 44	31. 46	25. 35	19. 87	19. 96	22. 43
γ 46. 0	12. 45	20. 02	27. 82	34. 54	32. 50	28. 71	38. 11	27. 18	21. 57	16. 65	16. 67	18. 95

**Photometric Filename:GL-3W-COB-0300-MH-60D-3000K-老化前.IES**

[illegible]



**Photometric Filename:GL-3W-COB-0300-MH-60D-3000K-老化前.IES**

[illegible]

**Photometric Filename:GL-3W-COB-0300-MH-60D-3000K-老化前.IES**

[illegible]